



Programming (via serial port):  
 Fit BOOT0 link (J301)  
 Disconnect OLED display (J302) if fitted  
 Connect J303 pin-1 to FTDI RxD (Yellow)  
 Connect J303 pin-2 to FTDI TxD (Orange)

Original Refs used where possible, 200 series for FDC and 300 series for GOTEK

Itemref	Quantity	Title/Name, designation, material, dimension etc	Article No./Reference
Drawn by: CDO		Filename: Atom FDC (Electron Case).dch	December 2023 Scale 1:1
Replica Acorn Atom Floppy Disc Controller PCB For Electron Enclosure		Replica Acorn Atom	
			Sheet 1/1